



# YA442NFXB, Cu Compression, 2-Hole, 1/2" Stud, 1-3/4" Spacing, Long Barrel, 750 kcmil G, H, 777 DLO



By Burndy  
Catalog # YA442NFXB

750 kcmil G,H,777 DLO CU, Two Hole, 1/2 Stud Size, 1-3/4 Hole Spacing, Long Barrel, Bell End, Tin Plated, UL/CSA, 90°C, Up to 35kV, Yellow Color Code, L115 Die Index.

## Features

- Barrel designed with internal chamfer at wire entry for smooth insertion of wire, preventing possible damage of the strands
- Long barrel length allows for an increased number of crimps increasing the mechanical strength of the connection
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding
- 2-Hole design prevents rotation

## Application

Wire Termination

## General

Catalog Number	YA442NFXB
Color Code	Yellow
Connector Type	LONG BARREL
Die Index	L115
EU RoHS Indicator	Yes
Feature - Barrel Style	Belled
Feature - Barrel Type	Long
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	2
Physical Attribute - Tongue Type	Standard
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	HYLUG
Temperature Rating	194
Trade Name	HYLUG™
Type	Long Barrel, Tin Plated
UPC	781810053584
UPC 12 Digit	7818100535844

## Dimensions

Dimension - B Length inch	3.33 in
Dimension - Bolt Hole Size inch	0.52 in
Dimension - Bolt Size fraction	1/2
Dimension - Bolt Size inch	0.5
Dimension - D inch	3.01 in
Dimension - Hole Size fraction	1/2
Dimension - Hole Size inch	0.56
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	189 mm
Dimension - Length Overall inch	7.44 in
Dimension - N inch	0.62 in
Dimension - Outside Diameter inch	1.50 in
Dimension - Pad Width inch	2.19 in
Dimension - Strip Length inch	3-7/16 in
Dimension - Stud Size fraction	1/2
Dimension - Stud Size inch	1/2 in
Dimension - Z (inch)	0.64 in
Physical Attribute - Tongue Angle	Straight

## Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

## Conductor Related

Conductor - Copper DLO Size	777 KCMIL
Conductor - Copper DLO Size	777 kcmil
Range	
Conductor - Copper Flex G Size	750 KCMIL
Conductor - Copper Flex G Size	750 kcmil
Range	
Conductor - Copper Flex H Size	750 KCMIL
Conductor - Copper Flex H Size	750 kcmil
Range	
Conductor - Copper Flex I Size	750 KCMIL
Conductor - Copper Flex I Size	750 kcmil
Range	
Conductor - Copper Str Size	750 KCMIL
Conductor - Copper Str Size	750 kcmil
Range	
Conductor - Material	COPPER
Conductor Size	750 KCMIL
Conductor Type	FLEX
Wire Size	750 KCMIL

## Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	Yes
Industry Standard(s)	UL 486A-486B
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

## Logistics

Carton Quantity	18
Minimum Pack Quantity	1
Pallet Quantity	1296

## Product Assets

[3D Models - YA442NFXB\\_MODEL-PDF](#)  
[3D Models - YA442NFXB\\_MODEL-IGES](#)  
[3D Models - YA442NFXB\\_MODEL-STEP](#)  
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Catalogs - BURNDY Master Catalog - Section C - Compression Connections](#)  
[Customer Notices - Prop 65 Notice](#)  
[Installation Manuals - Copper Flex Long Terminals Tooling and Installation Instructions](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Sales Drawings - SE..208074-01](#)  
[Video - HYDENT Compression Terminal Overview Video](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
BRDY-YA442NFXB-SPEC-EN | REV 8/2024