



Nylon Ring Terminal For 22 - 18 AWG

By Burndy
Catalog # [YAE18NBK](#)



Nylon Ring Terminal For 22 - 18 AWG.

General

Color Code	Red
Connector Type	Ring Terminal
Insulation	Y
Insulation Type	Nylon
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin
Trade Name	INSULUG™
UPC	781810030875
UPC 12 Digit	7818100308755

Dimensions

Dimension - Bolt Size fraction	#8 - #10
Dimension - Hole Size fraction	1/5
Dimension - Hole Size inch	0.20 in
Dimension - L Length Overall mm	23 mm
Dimension - Length Overall inch	0.92 in
Dimension - N inch	0.16 in
Dimension - Pad Width inch	0.31 in
Dimension - Strip Length inch	3/16 in
Dimension - Stud Size inch	#8;#10
Dimension - Width inch	0.06 in
Dimension - Z inch	0.28 in

Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

Conductor Related

Conductor - Copper Str Aircraft Size Range	AN22 - AN16
Conductor - Copper Str Size Range	22 AWG - 16 AWG
Conductor Size	22 - 18 AWG
Conductor Type	CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	Yes
Certification - cULus	No
Industry Standard(s)	<ul style="list-style-type: none">UL486Military Specified (Mil-Spec)
Standards - Industry Standards Met	UL486;Military Specified (Mil-Spec)
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	1000
Minimum Pack Quantity	1000
Pallet Quantity	99999

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Technical Solutions - BURNDY_YAE18NBK_Specsheet](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-YAE18NBK-SPEC-EN | REV 1/2024