

Nylon Ring Terminal For 26 - 20 AWG

By Burndy
Catalog # [YAE22G12](#)



Nylon Ring Terminal For 26 - 20 AWG.

Application

Types YAE-G and YAE-N terminals are rated 105 Deg C and meet military standard AS25036 Class 2 and SAE-AS7928 requirements

General

Color Code	Amber
Connector Type	Ring Terminal
EU RoHS Indicator	Yes
Feature - Barrel Style	Shrouded
Insulation	Y
Insulation Type	Nylon
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin
Sub Brand	INSULUG
Trade Name	INSULUG™
Type	YAE-G
UPC	781810804636
UPC 12 Digit	7818108046366

Dimensions

Dimension - Bolt Size fraction	#2
Dimension - Hole Size fraction	1/11
Dimension - Hole Size inch	0.09 in
Dimension - Length Overall inch	0.74 in
Dimension - N inch	0.12 in
Dimension - Pad Width inch	0.25 in
Dimension - Strip Length inch	5/32 in
Dimension - Stud Size inch	#2
Dimension - Z inch	0.22 in

Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

Conductor Related

Conductor - Copper Str Aircraft Size	AN 26;AN 22;AN 20
Conductor - Copper Str Size Range	26 AWG-20 AWG
Conductor Size	26 - 20 AWG
Conductor Type	CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	Military Specified (Mil-Spec)
Standards - Industry Standards Met	Military Specified (Mil-Spec)
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	1000
Minimum Pack Quantity	1000
Pallet Quantity	99999

Product Assets

[3D Models - YAE22G12_MODEL-PDF](#)
[3D Models - YAE22G12_MODEL-STEP](#)
[3D Models - YAE22G12_MODEL-IGES](#)
[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - 50094156](#)
[Technical Solutions - BURNDY_YAE22G12_Specsheet](#)

