

# Nylon Fork Terminal For 16 - 14 AWG

By Burndy  
Catalog # [YAES14N6F](#)



Nylon Fork Terminal For 16 - 14 AWG.

## Application

Power Connector

## General

Color Code	Blue
Connector Type	Fork Terminal
EU RoHS Indicator	Yes
Feature - Barrel Type	Standard
Insulation	Y
Insulation Type	Nylon
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Fork
Plated	Y
Plating Type	Tin
Sub Brand	INSULUG
Trade Name	INSULUG™
Type	YAES-F
UPC	781810805138
UPC 12 Digit	7818108051388

## Dimensions

Dimension - Bolt Size fraction	#4 - #6
Dimension - Hole Size fraction	3/20
Dimension - Hole Size inch	0.15 in
Dimension - Length Overall inch	0.79 in
Dimension - N inch	0.14 in
Dimension - Pad Width inch	0.28 in
Dimension - Strip Length inch	7/32 in
Dimension - Stud Size inch	#4;#5;#6
Dimension - Z (inch)	0.24 in

## Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

## Conductor Related

Conductor - Copper Solid Size	16 AWG;15 AWG;14 AWG
Conductor - Copper Solid Size Range	16 AWG-14 AWG
Conductor - Copper Str Size	16 AWG;14 AWG
Conductor - Copper Str Size Range	16 AWG - 14 AWG
Conductor Size	16 - 14 AWG
Conductor Type	CU C Str-Size

## Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	<ul style="list-style-type: none"><li>UL486</li><li>Military Specified (Mil-Spec)</li></ul>
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Carton Quantity	1000
Minimum Pack Quantity	1000
Pallet Quantity	99999

## Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Product Cross Section Image\(s\) - BUR\\_YAES10N56F\\_LineArt](#)  
[Sales Drawings - 50094172](#)

