



Radiation Resistant Insulated Ring Terminal For 22 - 18 AWG

By Burndy
Catalog # [YAES18K1](#)



Radiation Resistant Insulated Ring Terminal For 22 - 18 AWG.

Application

For Class 1E Critical Circuits And Non-Critical Nuclear Associated Applications

General

Color Code	Red
Connector Type	Ring Terminal
EU RoHS Indicator	Yes
Feature - Barrel Style	Belled
Insulation	Y
Insulation Type	Radiation Resistant
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin
Sub Brand	INSULUG
Trade Name	INSULUG™
Type	Radiation Resistant KYNAR Ring Tongue
UPC	781810810507
UPC 12 Digit	7818108105077

Dimensions

Dimension - Bolt Size fraction	#6
Dimension - Hole Size fraction	3/20
Dimension - Hole Size inch	0.15 in
Dimension - L Length Overall mm	19 mm
Dimension - Length Overall inch	0.76 in
Dimension - Pad Width inch	0.23 in
Dimension - Strip Length inch	7/32 in
Dimension - Stud Size inch	#6
Dimension - Z (inch)	0.20 in

Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

Conductor Related

Conductor - Copper Solid Size	22 ;20 ;18 AWG
Conductor - Copper Solid Size Range	22 -18 AWG
Conductor - Copper Str Size	22 AWG;20 AWG;18 AWG
Conductor - Copper Str Size Range	22 AWG - 18 AWG
Conductor Size	22 - 18 AWG
Conductor Type	<ul style="list-style-type: none">• CU C Str-Size• CU C Solid-Size

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	1000
Minimum Pack Quantity	1000
Pallet Quantity	99999

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Product Cross Section Image\(s\) - BUR_YAES14K7_LineArt](#)
[Sales Drawings - 50094159](#)



A proud member of the Hubbell Family.

