



Nylon Ring Terminal For 22 - 18 AWG

By Burndy
Catalog # [YAES18N48](#)



Nylon Ring Terminal For 22 - 18 AWG.

Application

For use on copper compression connections

General

Color Code	Red
Connector Type	Ring Terminal
EU RoHS Indicator	Yes
Feature - Barrel Style	Skived
Insulation	Y
Insulation Type	Nylon
Material	Copper
Military Specification	MS25036
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	INSULUG
Trade Name	INSULUG™
Type	YAES
UPC	781810804926
UPC 12 Digit	7818108049266

Dimensions

Dimension - Bolt Size fraction	#3 - #4
Dimension - G inch	0.12 in
Dimension - Length Overall inch	0.76 in
Dimension - Outside Diameter inch	0.28 in
Dimension - Stud Size inch	#3 - #4
Dimension - Width inch	0.23 in

Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

Conductor Related

Conductor - Copper Str Size	22 AWG;20 AWG;18 AWG
Conductor - Copper Str Size Range	22 AWG - 18 AWG
Conductor Size	22 - 18 AWG
Conductor Type	CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	<ul style="list-style-type: none">UL486Military Specified (Mil-Spec)

Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	1000
Minimum Pack Quantity	1000
Pallet Quantity	99999

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Product Cross Section Image\(s\) - BUR_YAES10N11_LineArt](#)
[Sales Drawings - 50094155](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-YAES18N48-SPEC-EN | REV 5/2024

