

# Nylon Ring Terminal For 16 - 14 AWG

By Burndy  
Catalog # YAEV14T2



Nylon Ring Terminal For 16 - 14 AWG.

## General

Color Code	Blue
Connector Type	Ring Terminal
Construction Material - Main	Copper
EU RoHS Indicator	Contact Manufacturer
Finish Type	Tin-Plated
Insulation	Y
Insulation Type	Nylon
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	INSULUG
Trade Name	INSULUG™
Type	YAEV
UPC	781810082218
UPC 12 Digit	7818100822188

## Dimensions

Dimension - Bolt Size fraction	1/4
Dimension - Hole Size fraction	10/37
Dimension - Hole Size inch	0.27 in
Dimension - N inch	0.26 in
Dimension - Pad Width inch	0.38 in
Dimension - Stud Size inch	1/4
Dimension - Width inch	0.10 in
Dimension - Z (inch)	0.32 in

## Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

## Conductor Related

Conductor - Copper Str Aircraft Size	AN 18;AN 16;AN 14
Conductor - Copper Str Aircraft Size Range	AN 18-AN 14
Conductor - Copper Str Size	20AWG ,18 AWG, 16 AWG, 14 AWG
Conductor - Copper Str Size Range	20 AWG - 14 AWG
Conductor Size	16 - 14 AWG
Conductor Type	<ul style="list-style-type: none"> <li>• CU C Solid-Size</li> <li>• CU C Str-Size</li> </ul>

## Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	<ul style="list-style-type: none"> <li>• UL486</li> <li>• Military Specified (Mil-Spec)</li> </ul>

Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Carton Quantity	1000
Minimum Pack Quantity	1000
Pallet Quantity	99999

## Product Assets

[3D Models - YAEV14T2\\_MODEL-IGES](#)  
[3D Models - YAEV14T2\\_MODEL-STEP](#)  
[3D Models - YAEV14T2\\_MODEL-PDF](#)  
[Catalogs - Full Line BURNDY Catalog](#)  
[Sales Drawings - 50094163](#)

