

Nylon Ring Terminal For 8 AWG

By Burndy
Catalog # YAEV8CL14BOX

Nylon Ring Terminal For 8 AWG.



General

Color Code	Red
Connector Type	Ring Terminal
Die Index	435
Insulation	Y
Insulation Type	Nylon
Material	Copper
Military Specification	MS25036
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin
Temperature Rating	105°C
Trade Name	INSULUG™
UPC	781810023051
UPC 12 Digit	7818100230511

Dimensions

Dimension - B Length fraction	9/25 in
Dimension - B Length inch	0.36 in
Dimension - Bolt Size fraction	#8
Dimension - L Length Overall mm	36 mm
Dimension - Length Overall inch	1.40 in
Dimension - N inch	0.2 in
Dimension - P inch	0.13 in
Dimension - Pad Width inch	0.41 in
Dimension - Strip Length inch	7/16
Dimension - Stud Size inch	#8
Dimension - Z inch	0.28 in

Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

Conductor Related

Conductor - Copper Str Aircraft Size	AN 8
Conductor - Copper Str Aircraft Size Range	AN 8
Conductor - Copper Str Size	8 AWG
Conductor - Copper Str Size Range	8 AWG
Conductor Size	8 AWG
Conductor Type	<ul style="list-style-type: none"> • CU C Str Aircraft-Size • CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	<ul style="list-style-type: none"> • UL486 • Military Specified (Mil-Spec)
Standards - Industry Standards Met	<ul style="list-style-type: none"> • UL486 • Military Specified (Mil-Spec)
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	50
Minimum Pack Quantity	100

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Sales Drawings - 50094163](#)
[Technical Solutions - BURNDY_YAEV8CL14BOX_Specsheet](#)

