



Nylon Ring Terminal For 8 AWG (Silver Plated)

By Burndy
Catalog # [YAEV8CLSV](#)



Nylon Ring Terminal For 8 AWG (Silver Plated).

General

Color Code	Red
Connector Type	Ring Terminal
Insulation	Y
Insulation Type	Nylon
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Silver
Trade Name	INSULUG™
UPC	781810469828
UPC 12 Digit	7818104698288

Dimensions

Dimension - B Length fraction	9/25 in
Dimension - B Length inch	0.36 in
Dimension - Bolt Size fraction	#10
Dimension - Length Overall inch	1.40 in
Dimension - N inch	0.2 in
Dimension - P inch	0.13 in
Dimension - Pad Width inch	0.41 in
Dimension - Stud Size inch	#10
Dimension - Z inch	0.28 in

Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

Conductor Related

Conductor - Copper Str Aircraft Size	AN 8
Conductor - Copper Str Aircraft Size Range	AN 8
Conductor Size	8 AWG
Conductor Type	<ul style="list-style-type: none">CU C Str Aircraft-SizeCU C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	<ul style="list-style-type: none">UL486Military Specified (Mil-Spec)
Standards - Industry Standards Met	UL486;Military Specified (Mil-Spec)
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	200
Minimum Pack Quantity	200
Pallet Quantity	99999

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Technical Solutions - BURNDY_YAEV8CLSV_Specsheet](#)



A proud member of the Hubbell Family.