



YAG8CLTC516FX, Compression Terminal, 8 Flex G,H,I,K,M, DLO, 8 AWG, Cu, 1-Hole, 5/16" Stud, Standard Barrel



By Burndy
Catalog # [YAG8CLTC516FX](#)

8 Flex G,H,I,K,M,DLO, 8 AWG CU, One Hole, 5/16 Stud Size, Standard Barrel Internal Chamfer, Tin Plated, UL/CSA, 90°C, Up to 35kV, Red Color Code, 49 Die Index.

Application

Wire Termination

General

| | |
|--------------------------------------|-----------------------------|
| Catalog Number | YAG8CLTC516FX |
| Color Code | Red |
| Connector Type | STANDARD BARREL |
| Die Index | 49 |
| Feature - Barrel Style | Chamfered |
| Feature - Barrel Type | Standard |
| Finish Type | Tin-Plated |
| Material | COPPER |
| Physical Attribute - Number of Holes | 1 |
| Plated | Y |
| Plating Type | Tin - Electro Plated |
| Trade Name | HYLUG™ |
| Type | Standard Barrel, Tin Plated |
| UPC | 781810330623 |
| UPC 12 Digit | 7818103306233 |

Dimensions

| | |
|-----------------------------------|----------|
| Dimension - B Length fraction | 7/16 in |
| Dimension - B Length inch | 0.44 in |
| Dimension - Bolt Hole Size inch | 0.33 in |
| Dimension - Bolt Size fraction | 5/16 |
| Dimension - Bolt Size inch | 0.3125 |
| Dimension - D inch | 0.70 in |
| Dimension - Hole Size fraction | 5/16 |
| Dimension - Hole Size inch | 0.38 |
| Dimension - Hole Size mm | 10 mm |
| Dimension - L Length Overall mm | 35 mm |
| Dimension - Length Overall inch | 1.38 in |
| Dimension - N inch | 0.34 in |
| Dimension - Outside Diameter inch | 0.27 in |
| Dimension - Pad Width inch | 0.52 in |
| Dimension - Strip Length inch | 1/2 |
| Dimension - Stud Size fraction | 5/16 |
| Dimension - Stud Size inch | 5/16 |
| Dimension - Z (inch) | 0.36 in |
| Physical Attribute - Tongue Angle | Straight |

Electrical Ratings

| | |
|-------------------|-------|
| Voltage - Maximum | 35000 |
| Voltage Rating | 35 kV |

Conductor Related

| | |
|---|-------------------------|
| Conductor - Copper DLO Size | 8 AWG |
| Conductor - Copper DLO Size | 8 AWG |
| Range | |
| Conductor - Copper Flex G Size | "8 AWG" |
| Conductor - Copper Flex G Size | 8 AWG |
| Range | |
| Conductor - Copper Flex H Size | "8 AWG" |
| Conductor - Copper Flex H Size | 8 AWG |
| Range | |
| Conductor - Copper Flex I Size | "8 AWG" |
| Conductor - Copper Flex I Size | 8 AWG |
| Range | |
| Conductor - Copper Flex K Size | "8 AWG" |
| Conductor - Copper Flex K Size | 8 AWG |
| Range | |
| Conductor - Copper Flex M Size | "8 AWG" |
| Conductor - Copper Solid Size | 8-6 Sol |
| Range | |
| Conductor - Copper Str Compact Size | "8 AWG" |
| Conductor - Copper Str Navy Size | 23 |
| Conductor - Copper Str Size | "8 AWG" |
| Conductor - Copper Str Size | 8 AWG |
| Range | |
| Conductor - CopperWeld C Solid Size | 8 AWG |
| Conductor - CopperWeld Solid Size Range | 8 AWG |
| Conductor - CopperWeld Str Size | 8 A AWG;8 C AWG;8 D AWG |
| Conductor - Material | COPPER |
| Conductor Size | 8 AWG |
| Conductor Type | CODE/FLEX |
| Wire Size | 8 AWG |

Certifications And Compliance

| | |
|-------------------------------|--------------|
| Certification - CSA Approved | Yes |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Industry Standard(s) | UL 486A-486B |
| Standards - RoHS Compliance | CM |
| Status | |
| UL Listed | Yes |

Logistics

| | |
|-----------------------|----|
| Carton Quantity | 50 |
| Minimum Pack Quantity | 50 |

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section C - Compression Connections](#)
[Customer Notices - Prop 65 Notice](#)
[Installation Manuals - Copper Flex Standard Terminals Tooling and Installation Instructions](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 50000268](#)
[Specifications - YAG8CLTC516FX](#)
[Video - HYDENT Compression Terminal Overview Video](#)



A Hubbell brand