

Compression Terminal

By Burndy
Catalog # YAGB25LTC12FX

1 Hole HYLUG Cu Battery Terminal, 1/0 AWG, 1/2" stud, 2.40" L, 0.87" W, Black.



Application

Wire Termination

General

Color Code	Pink
Connector Type	GROUNDING/STARTER LUGS
Die Index	12
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	1
Plated	Yes
Plating Type	Tin Plated
Trade Name	HYLUG™
Type	OEM Terminals
UPC	781810562857
UPC 12 Digit	7818105628577

Dimensions

Dimension - Bolt Hole Size inch	0.52 in
Dimension - Bolt Size fraction	1/2
Dimension - Bolt Size inch	0.5
Dimension - Hole Size fraction	1/2
Dimension - Hole Size inch	0.53
Dimension - Hole Size mm	13.5 mm
Dimension - L Length Overall mm	61 mm
Dimension - Length Overall inch	2.40 in
Dimension - Strip Length inch	1-3/16 in
Dimension - Stud Size fraction	1/2
Dimension - Stud Size inch	1/2 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper DLO Size	1/0 AWG
Conductor - Copper DLO Size Range	1/0 AWG
Conductor - Copper Flex G Size	1/0 AWG
Conductor - Copper Flex G Size Range	1/0 AWG
Conductor - Copper Flex H Size	1/0 AWG
Conductor - Copper Flex H Size Range	1/0 AWG
Conductor - Copper Flex I Size	1/0 AWG
Conductor - Copper Flex I Size Range	1/0 AWG
Conductor - Copper Flex K Size	1/0 AWG
Conductor - Copper Flex K Size Range	1/0 AWG
Conductor - Copper Flex M Size	1/0 AWG
Conductor - Copper Str Size	1/0 AWG
Conductor - Copper Str Size Range	1/0 AWG
Conductor - Material	COPPER
Conductor Size	1/0 AWG
Conductor Type	CODE/FLEX
Wire Size	1/0 AWG

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	200
Minimum Pack Quantity	20

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Sales Drawings - 50004537](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-YAGB25LTC12FX-SPEC-EN | REV 8/2023