

Uninsulated Ring Terminal For 22 - 18 AWG

By Burndy
Catalog # [YAD18516](#)



Uninsulated Ring Terminal For 22 - 18 AWG.

Application

For control wiring and other standard duty applications

General

Connector Type	Ring Terminal
EU RoHS Indicator	Yes
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Long
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	HYLUG
Trade Name	HYLUG™
Type	Ring Tongue
UPC	781810806272
UPC 12 Digit	7818108062722

Dimensions

Dimension - Bolt Size fraction	5/16
Dimension - Hole Size fraction	8/25
Dimension - Hole Size inch	0.32 in
Dimension - L Length Overall mm	24 mm
Dimension - Length Overall inch	0.96 in
Dimension - Pad Width inch	0.46 in
Dimension - Strip Length inch	9/32 in
Dimension - Stud Size inch	5/16
Dimension - Z inch	0.44 in

Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

Conductor Related

Conductor - Copper Str Size Range	22 AWG - 18 AWG
Conductor Size	22 - 18 AWG
Conductor Type	CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	1000
Minimum Pack Quantity	1000
Pallet Quantity	99999

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - 50094154](#)