



YAK311A2G1, Aluminum - Compression Stacking Terminal (HYLUG Terminal)

By Burndy
Catalog # YAK311A2G1



Aluminum Stacking compression terminal, 397.5 Kcmil, 7.75 IN L, Up to eight conductors can be stacked on one 4 hole pad.

General

Connector Type	Terminal
Die Index	317;705
Feature - Barrel Style	Chamfered
Material	Aluminum Alloy
Physical Attribute - Number of Crimps Required	2
Physical Attribute - Number of Holes	2
Physical Attribute - Tongue Type	Standard
Plated	N
Plating Type	Unplated
Trade Name	HYLUG™
UPC	781810187104
UPC 12 Digit	7818101871044

Dimensions

Dimension - B Length inch	2.41 in
Dimension - Bolt Hole Size inch	0.50 in
Dimension - D inch	3.06 in
Dimension - Hole Size inch	0.56 in
Dimension - L Length Overall mm	197 mm
Dimension - Length Overall inch	7.75 in
Dimension - N inch	0.62 in
Dimension - Outside Diameter inch	1.25 in
Dimension - Pad Width inch	1.62 in
Dimension - Strip Length inch	2-1/2 in
Physical Attribute - Tongue Angle	Offset

Conductor Related

Conductor - AL Str Size	397.5 kcmil
Conductor - AL Str Size Range	397.5 kcmil
Conductor - Copper Str Size	397.5 kcmil
Conductor - Copper Str Size Range	397.5 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	6
-----------------------	---

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - SD59493-01](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-YAK311A2G1-SPEC-EN | REV 8/2023