



Uninsulated Ring Terminal For 400 - 450 kcmil

By Burndy
Catalog # [YAD33M20E34](#)



Uninsulated Ring Terminal For 400 - 450 kcmil.

Application

The YAD uninsulated OEM lug terminal is constructed of electrolytic copper

General

Connector Type	Ring Terminal
EU RoHS Indicator	No
Feature - Barrel Type	Long
Material	Copper
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin
Sub Brand	TERMINALS, HYLUG
Trade Name	HYLUG™
Type	Ring Tongue
UPC	781810549292
UPC 12 Digit	7818105492922

Dimensions

Dimension - B Length inch	1.26 in
Dimension - Bolt Size fraction	3/4
Dimension - Hole Size inch	0.80 in
Dimension - L Length Overall mm	76 mm
Dimension - Length Overall inch	3.01 in
Dimension - Outside Diameter inch	1.24 in
Dimension - Pad Width inch	1.50 in
Dimension - Strip Length inch	1-3/8
Dimension - Stud Size inch	3/4

Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

Conductor Related

Conductor - Copper Str Size	400 kcmil;450 kcmil
Conductor - Copper Str Size Range	400 kcmil - 450 kcmil
Conductor Type	<ul style="list-style-type: none">• CU C Str-Size• CU C Flex-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	100
Minimum Pack Quantity	10

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - 50013876](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-YAD33M20E34-SPEC-EN | REV 8/2023