



# Compression Terminal

By Burndy  
Catalog # [YAV150FM10](#)

Non Insulated Cu Tubular Terminal, 1 Hole, W/Insp Window, 150 mm, 10 mm Stud, 2.50 IN L, Compression, 17 Index, 29 mm Strip Length.



## Application

Metric Wire Termination

## General

Connector Type	METRIC
Die Index	17
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Metric Terminals
UPC	781810322031
UPC 12 Digit	7818103220311

## Dimensions

Dimension - B Length inch	1.06 in
Dimension - Bolt Size fraction	3/8
Dimension - Bolt Size inch	0.38
Dimension - Hole Size fraction	3/8
Dimension - Hole Size inch	0.41
Dimension - Hole Size mm	10.4 mm
Dimension - L Length Overall mm	64 mm
Dimension - Length Overall inch	2.5 in
Dimension - N inch	0.28 in
Dimension - Outside Diameter inch	0.88 in
Dimension - Pad Width inch	1.29 in
Dimension - Strip Length inch	1.14 in
Dimension - Stud Size fraction	3/8
Dimension - Z (inch)	0.42 in
Physical Attribute - Tongue Angle	Straight

## Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

## Conductor Related

Conductor - Copper Str Size	150 mm2
Conductor - Material	COPPER
Conductor Size	150 mm2
Conductor Type	CLASS 5

## Certifications And Compliance

Standards - RoHS Compliance Status	CM
------------------------------------	----

## Logistics

Minimum Pack Quantity	100
-----------------------	-----

## Product Assets

[3D Models - YAV150FM10\\_MODEL-STEP](#)  
[3D Models - YAV150FM10\\_MODEL-IGES](#)  
[3D Models - YAV150FM10\\_MODEL-PDF](#)  
[Catalogs - Full Line BURNDY Catalog](#)  
[Product Cross Section Image\(s\) - BUR\\_yavm\\_lineart](#)  
[Sales Drawings - 50025612](#)



