

# Nylon Fork Terminal For 22 - 18 AWG

By Burndy  
Catalog # YAE18N60F



Nylon Fork Terminal For 22 - 18 AWG.

## General

Color Code	Red
Connector Type	Fork Terminal
Insulation	Y
Insulation Type	Nylon
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Fork
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	INSULUG™
UPC	781810034750
UPC 12 Digit	7818100347500

## Dimensions

Dimension - B Length fraction	4/25 in
Dimension - B Length inch	0.16 in
Dimension - Bolt Size fraction	#4
Dimension - Hole Size fraction	3/25
Dimension - Hole Size inch	0.12 in
Dimension - Length Overall inch	0.92 in
Dimension - N inch	0.19 in
Dimension - Pad Width inch	0.21 in
Dimension - Strip Length inch	3/16 in
Dimension - Stud Size inch	#4
Dimension - Z inch	0.24 in

## Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

## Conductor Related

Conductor - Copper Str Aircraft Size	AN 22;AN 20;AN 18;AN 16
Conductor - Copper Str Size	20 AWG;18 AWG;16 AWG
Conductor - Copper Str Size Range	20 AWG - 16 AWG
Conductor Size	22 - 18 AWG
Conductor Type	CU C Str-Size

## Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	<ul style="list-style-type: none"> <li>• UL486</li> <li>• Military Specified (Mil-Spec)</li> </ul>
Standards - Industry Standards Met	<ul style="list-style-type: none"> <li>• UL486</li> <li>• Military Specified (Mil-Spec)</li> </ul>
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Carton Quantity	1000
Minimum Pack Quantity	1000
Packaging Type	Bulk
Pallet Quantity	99999

## Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Sales Drawings - 50094173](#)  
[Technical Solutions - BURNDY\\_YAE18N60F\\_Specsheet](#)

