

Uninsulated Right Angle Ring Terminal For 4/0 AWG

By Burndy
Catalog # [YAV28RS](#)



Uninsulated Right Angle Ring Terminal For 4/0 AWG.

Application

For Use On Copper Commercial (Code) Cable, Type AN Aircraft Cable And Extra Flexible Conductors

General

Connector Type	Ring Terminal
Die Index	46
EU RoHS Indicator	Yes
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin
Sub Brand	TERMINALS, HYLUG
Trade Name	HYLUG™
Type	Ring Tongue
UPC	781810025895

Dimensions

Dimension - B Length fraction	7/8 in
Dimension - B Length inch	0.88 in
Dimension - Bolt Hole Size inch	0.39 in
Dimension - Bolt Size fraction	3/8
Dimension - G inch	1.54 in
Dimension - Hole Size mm	10 mm
Dimension - L Length Overall mm	44 mm
Dimension - Length Overall inch	1.75 in
Dimension - N inch	0.48 in
Dimension - Outside Diameter inch	0.78 in
Dimension - Pad Width inch	1.12 in
Dimension - Strip Length inch	7/8
Dimension - Stud Size inch	3/8
Dimension - Z inch	0.47 in
Physical Attribute - Tongue Angle	90 Degree

Conductor Related

Conductor - Copper Str Aircraft Size	AN-4/0
Conductor - Copper Str Size	4/0
Conductor - Copper Str Size Range	4/0 AWG
Conductor Size	4/0 AWG
Conductor Type	<ul style="list-style-type: none"> • CU C Solid-Size • CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	100
Minimum Pack Quantity	100
Pallet Quantity	15000

Product Assets

[Sales Drawings - 50094166](#)

