



Nylon Ring Terminal For 26 - 20 AWG

By Burndy
Catalog # [YAE22G15BOX](#)



Nylon Ring Terminal For 26 - 20 AWG.

General

Color Code	Amber
Connector Type	Ring Terminal
Insulation	Y
Insulation Type	Nylon
Material	Copper
Military Specification	MS25036
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin
Trade Name	INSULUG™
UPC	781810023242
UPC 12 Digit	7818100232422

Dimensions

Cable Insulation Diameter Maximum	0.098 in
Dimension - Bolt Size fraction	#8 - #10
Dimension - Hole Size fraction	1/5
Dimension - Hole Size inch	0.20 in
Dimension - L Length Overall mm	21 mm
Dimension - Length Overall inch	0.83 in
Dimension - N inch	0.16 in
Dimension - Pad Width inch	0.32 in
Dimension - Strip Length inch	5/32
Dimension - Stud Size inch	#8;#10
Dimension - Z (inch)	0.27 in

Electrical Ratings

Voltage - Maximum	300 V
-------------------	-------

Conductor Related

Conductor - Copper Str Aircraft Size	AN 26;AN 22;AN 20
Conductor Range	#26 AWG to #20 AWG
Conductor Size	26 - 20 AWG
Conductor Type	<ul style="list-style-type: none">• CU C Str-Size• CU C Solid-Size

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	Military Specified (Mil-Spec)
Standards - Industry Standards Met	Military Specified (Mil-Spec)
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	1200
Minimum Pack Quantity	100
Pallet Quantity	99999

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Product Cross Section Image\(s\) - BUR_YAE22G15BOX_LineArt](#)
[Sales Drawings - 50094156](#)



A proud member of the Hubbell Family.