



Nylon Fork Terminal For 26 - 20 AWG

By Burndy
Catalog # [YAE22N65FBOX](#)



Nylon Fork Terminal For 26 - 20 AWG.

Application

Power Connector

General

Color Code	Amber
Connector Type	Fork Terminal
Feature - Barrel Style	Shrouded
Insulation	Y
Insulation Type	Nylon
Material	Copper
Physical Attribute - Tongue Type	Fork
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	INSULUG™
UPC	781810023211
UPC 12 Digit	7818100232111

Dimensions

Cable Insulation Diameter Maximum	0.098 in
Dimension - B Length fraction	10/91 in
Dimension - B Length inch	0.11 in
Dimension - Bolt Size fraction	#2
Dimension - Hole Size fraction	1/11
Dimension - Hole Size inch	0.09 in
Dimension - L Length Overall mm	19 mm
Dimension - Length Overall inch	0.73 in
Dimension - N inch	0.09 in
Dimension - Pad Width inch	0.18 in
Dimension - Strip Length inch	5/32 in
Dimension - Stud Size inch	#2
Dimension - Z inch	0.22 in

Electrical Ratings

Voltage - Maximum 600 V

Conductor Related

Conductor - Copper Str Aircraft Size	AN 26;AN 22;AN 20
Conductor - Copper Str Size	20
Conductor - Copper Str Size Range	24 AWG-20 AWG
Conductor Size	26 - 20 AWG

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	Yes
Certification - cULus	No
Industry Standard(s)	Military Specified (Mil-Spec)
Standards - Industry Standards Met	Military Specified (Mil-Spec)
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	1200
Minimum Pack Quantity	100
Pallet Quantity	99999

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - 50094173](#)
[Technical Solutions - BURNDY_YAE22N65FBOX_Specsheet](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-YAE22N65FBOX-SPEC-EN | REV 1/2024

