

Compression Terminal

By Burndy
Catalog # [YAV95FM12](#)

Non Insulated Cu Tubular Terminal, 1 Hole, W/Insp Window, 95 mm, 12 mm Stud, 2.59 IN L, Compression, 14 Index, 27 mm Strip Length.



Application

Metric Wire Termination

General

Connector Type	METRIC
Die Index	14
Feature - Barrel Style	<ul style="list-style-type: none"> • Chamfered • Skived
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Metric Terminals
UPC	781810243022
UPC 12 Digit	7818102430222

Dimensions

Dimension - B Length fraction	1 in
Dimension - B Length inch	1.00 in
Dimension - Bolt Size fraction	1/2
Dimension - Bolt Size inch	0.5
Dimension - D inch	1.04 in
Dimension - Hole Size fraction	1/2
Dimension - Hole Size inch	0.53
Dimension - Hole Size mm	13.5 mm
Dimension - Inside Diameter inch	0.56 in
Dimension - L Length Overall mm	66 mm
Dimension - Length Overall inch	2.59 in
Dimension - N inch	0.53 in
Dimension - Outside Diameter inch	0.70 in
Dimension - Pad Width inch	1.03 in
Dimension - Strip Length inch	1.06 in
Dimension - Stud Size fraction	1/2
Dimension - Stud Size inch	#12
Dimension - Z inch	0.55 in
Physical Attribute - Tongue	Straight

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper Str Size	2/0 AWG
Conductor - Material	COPPER
Conductor Size	95 mm ²
Conductor Type	CLASS 5

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	10
Minimum Pack Quantity	100

Product Assets

[3D Models - YAV95FM12_MODEL-STEP](#)
[3D Models - YAV95FM12_MODEL-PDF](#)
[3D Models - YAV95FM12_MODEL-IGES](#)
[Catalogs - Full Line BURNDY Catalog](#)
[Sales Drawings - 50025612](#)



A proud member of the Hubbell Family.