

Compression Terminal

By Burndy
Catalog # [YAV95M8](#)

Copper Tubing Terminal, 1 Hole W/insp window, 95 mm Class 2, 14 Index, 8 mm Stud.



Application

Metric Wire Termination

General

Connector Type	METRIC
Die Index	14
Feature - Barrel Style	<ul style="list-style-type: none"> • Chamfered • Skived
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Metric Terminals
UPC	781810324141
UPC 12 Digit	7818103241411

Dimensions

Dimension - B Length inch	0.81 in
Dimension - Bolt Size fraction	5/16
Dimension - Bolt Size inch	0.3125
Dimension - Hole Size fraction	5/16
Dimension - Hole Size inch	0.38
Dimension - Hole Size mm	10 mm
Dimension - L Length Overall mm	50.3
Dimension - Length Overall inch	1.98
Dimension - N inch	0.34
Dimension - Outside Diameter inch	0.63
Dimension - Pad Width inch	0.93 in
Dimension - Strip Length inch	0.87 in
Dimension - Stud Size fraction	5/16
Dimension - Z inch	0.36 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper Str Size Range	95 mm ² , 2/0 AWG
Conductor - Material	COPPER
Conductor Size	95 mm ²
Conductor Type	CLASS 2

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	10
Minimum Pack Quantity	10

Product Assets

[3D Models - YAV95M8_MODEL-STEP](#)
[3D Models - YAV95M8_MODEL-PDF](#)
[3D Models - YAV95M8_MODEL-IGES](#)
[Sales Drawings - 50025521](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-YAV95M8-SPEC-EN | REV 8/2023