

Nylon Ring Terminal For 2/0 AWG

By Burndy
Catalog # YAEV26L1

Nylon Ring Terminal For 2/0 AWG.



Application

For Very Demanding High Vibration Applications Encountered In Aircraft And Aboard Ships As Well As Motor Lead Applications In Hospitals, Industrials And Generating Plants

General

Color Code	Yellow
Connector Type	Ring Terminal
Die Index	601
EU RoHS Indicator	Yes
Feature - Barrel Style	Belled
Feature - Barrel Type	Standard
Insulation	Y
Insulation Type	Nylon
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin
Sub Brand	INSULUG
Trade Name	INSULUG™
Type	YAEV-L, Heavy Duty
UPC	781810027660
UPC 12 Digit	7818100276600

Dimensions

Dimension - B Length inch	0.75 in
Dimension - Bolt Size fraction	1/4
Dimension - Length Overall inch	2.75 in
Dimension - N inch	0.47 in
Dimension - P inch	0.3 in
Dimension - Pad Width inch	0.93 in
Dimension - Stud Size inch	1/4
Dimension - Z inch	0.48 in

Conductor Related

Conductor - Copper Str Aircraft Size	AN 2/0
Conductor - Copper Str Size	2/0 AWG
Conductor Size	2/0 AWG
Conductor Type	<ul style="list-style-type: none"> • CU C Solid-Size • CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	<ul style="list-style-type: none"> • UL486 • Military Specified (Mil-Spec)
Standards - Industry Standards Met	<ul style="list-style-type: none"> • UL486 • Military Specified (Mil-Spec)
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	100
Minimum Pack Quantity	100
Pallet Quantity	24000

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Sales Drawings - 50094163](#)
[Technical Solutions - BURNDY_YAEV26L1_Specsheet](#)

