

Compression Terminal

By Burndy
Catalog # [YAG32L2TC38LD](#)

Cu Tubing HYLUG™, 2 Holes, Lead Plated.



Application

Wire Termination

General

Color Code	Blue
Connector Type	STANDARD BARREL
Die Index	18
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Finish Type	Lead Plated
Material	COPPER
Physical Attribute - Number of Holes	2
Plated	Y
Plating Type	Lead Plated
Temperature Rating	194
Trade Name	HYLUG™
Type	Standard Barrel, Lead Plated
UPC	781810320136
UPC 12 Digit	7818103201366

Dimensions

Dimension - B Length inch	1.19 in
Dimension - Bolt Size fraction	3/8
Dimension - Bolt Size inch	0.38
Dimension - Hole Size fraction	3/8
Dimension - Hole Size inch	0.41
Dimension - Hole Size mm	10.4 mm
Dimension - L Length Overall mm	95 mm
Dimension - Length Overall inch	3.73 in
Dimension - N inch	0.41 in
Dimension - Outside Diameter inch	0.95 in
Dimension - Pad Width inch	1.40 in
Dimension - Stud Size fraction	3/8
Dimension - Stud Size inch	3/8
Dimension - Z inch	0.43 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper DLO Size	313 KCMIL
Conductor - Copper Flex G Size	300 KCMIL
Conductor - Copper Flex H Size	300 KCMIL
Conductor - Copper Flex I Size	300 KCMIL
Conductor - Copper Flex K Size	300 KCMIL
Conductor - Copper Flex M Size	300 KCMIL
Conductor - Copper Flex M Size Range	300 kcmil
Conductor - Copper Str Size	300 KCMIL
Conductor - Copper Str Size Range	400 kcmil
Conductor - Material	COPPER
Conductor Size	300 KCMIL
Conductor Type	FLEX
Wire Size	300 KCMIL

Certifications and Compliance

Industry Standard(s)	UL 486A-486B
Standards - RoHS Compliance Status	NC

Logistics

Minimum Pack Quantity	200
-----------------------	-----

Product Assets

[Sales Drawings - SE207958](#)

[Video - HYDENT Compression Terminal Overview Video](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-YAG32L2TC38LD-SPEC-EN | REV 8/2023