



YAK361A2G1, Aluminum - Compression Stacking Terminal (HYLUG Terminal)



By Burndy
Catalog # [YAK361A2G1](#)

Aluminum Stacking compression terminal, 600 Kcmil, 8.22 IN L,
Up to eight conductors can be stacked on one 4 hole pad.

General

Catalog Number	YAK361A2G1
Connector Type	Terminal
Die Index	608;722;786
Feature - Barrel Style	Chamfered
Material	Aluminum Alloy
Physical Attribute - Number of Crimps Required	1
Physical Attribute - Number of Holes	2
Physical Attribute - Tongue Type	Standard
Plated	N
Plating Type	Unplated
Trade Name	HYLUG™
UPC	781810081723
UPC 12 Digit	7818100817233

Dimensions

Dimension - B Length inch	2.65 in
Dimension - Bolt Hole Size inch	0.50 in
Dimension - D inch	3.06 in
Dimension - Hole Size inch	0.56 in
Dimension - L Length Overall mm	209 mm
Dimension - Length Overall inch	8.22 in
Dimension - N inch	0.62 in
Dimension - Outside Diameter inch	1.5 in
Dimension - Pad Width inch	1.62 in
Dimension - Strip Length inch	2-11/16 in
Physical Attribute - Tongue Angle	Offset

Conductor Related

Conductor - AL Str Size	600 kcmil
Conductor - AL Str Size Range	600 kcmil
Conductor - Copper Str Size	600 kcmil
Conductor - Copper Str Size Range	600 kcmil

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section H - Overhead Distribution](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - SD59493-01](#)
- [Specifications - YAK361A2G1](#)