



YBM26L2, Uninsulated Flag-Type Ring Terminal For 2/0 AWG

By Burndy
Catalog # [YBM26L2](#)

Uninsulated Flag-Type Ring Terminal For 2/0 AWG.



Features

- Made of pure electrolytic copper for maximum conductivity and ductility
- Seamless extrusion tin plated to resist corrosion
- Beveled barrel for easy wire entry

General

Catalog Number	YBM26L2
Connector Type	Flag Ring Terminal
Die Index	598
Feature - Barrel Style	Chamfered
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
UPC	781810455586

Dimensions

Dimension - B Length fraction	13/16 in
Dimension - B Length inch	0.78 in
Dimension - Bolt Hole Size inch	0.27 in
Dimension - Bolt Size fraction	1/4
Dimension - Length Overall inch	1.66 in
Dimension - N inch	0.33 in
Dimension - Outside Diameter inch	0.76 in
Dimension - Pad Width inch	0.84 in
Dimension - Stud Size inch	1/4 in
Dimension - Z (inch)	0.45 in
Physical Attribute - Tongue Angle	90 Degree

Conductor Related

Conductor - Copper Str Aircraft Size	AN 2/0
Conductor - Copper Str Size	2/0
Conductor - Copper Str Size Range	2/0 AWG
Conductor Size	2/0 AWG
Conductor Type	<ul style="list-style-type: none">• CU C Solid-Size• CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	100
Minimum Pack Quantity	100
Pallet Quantity	24000

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 50094169](#)



A Hubbell brand