



Uninsulated Flag-Type Ring Terminal For 2/0 AWG (Nickel Plated)

By Burndy
Catalog # [YBM26L3NK](#)



Uninsulated Flag-Type Ring Terminal For 2/0 AWG (Nickel Plated).

General

Connector Type	Flag Ring Terminal
Die Index	598
Feature - Barrel Style	Chamfered
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Nickel
Trade Name	HYLUG™
UPC	781810463178

Dimensions

Dimension - B Length fraction	7/8 in
Dimension - B Length inch	0.84 in
Dimension - Bolt Hole Size inch	0.52 in
Dimension - Bolt Size fraction	1/2
Dimension - Length Overall inch	1.96 in
Dimension - N inch	0.48 in
Dimension - Outside Diameter inch	0.76 in
Dimension - Pad Width inch	0.91 in
Dimension - Stud Size inch	1/2 in
Dimension - Z inch	0.61 in
Physical Attribute - Tongue Angle	90 Degree

Conductor Related

Conductor - Copper Str Aircraft Size	AN 2/0
Conductor - Copper Str Size	2/0
Conductor - Copper Str Size Range	2/0 AWG
Conductor Size	2/0 AWG
Conductor Type	<ul style="list-style-type: none">• CU C Solid-Size• CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	100
Minimum Pack Quantity	100
Pallet Quantity	19600

Product Assets

[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - 03073901](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-YBM26L3NK-SPEC-EN | REV 8/2023