

YCA252N

By Burndy
Catalog # [YCA252N](#)

Copper compression lug designed for terminating copper conductors to switch pads and other substation switch yard apparatus, 5-3/8 IN L.



Application

Designed for terminating copper conductors to switch pads and other substation or switch yard apparatus

General

Connector Type	Terminal
Die Index	165
EU RoHS Indicator	Yes
Material	Copper
Physical Attribute - Number of Crimps Required	1
Physical Attribute - Number of Holes	2
Physical Attribute - Tongue Type	Standard
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	N
Sub Brand	TERMINALS, HYLUG
Trade Name	HYLUG™
Type	YCA-2N
UPC	781810810385
UPC 12 Digit	7818108103855

Dimensions

Dimension - B Length fraction	1-4/7 in
Dimension - B Length inch	1.57 in
Dimension - D inch	3.00 in
Dimension - Hole Size fraction	5/9
Dimension - Hole Size inch	0.56 in
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	136 mm
Dimension - Length Overall inch	5.34 in
Dimension - N inch	0.63 in
Dimension - Outside Diameter inch	0.62 in
Dimension - Pad Width inch	0.91 in
Dimension - Strip Length inch	1 5/8
Dimension - Z inch	2.37 in
Physical Attribute - Tongue Angle	Straight

Conductor Related

Conductor - Copper Str Size	1/0
Conductor - Copper Str Size Range	1/0

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	50
Minimum Pack Quantity	1
Pallet Quantity	7400

Product Assets

[3D Models - YCA252N_MODEL-IGES](#)
[3D Models - YCA252N_MODEL-PDF](#)
[3D Models - YCA252N_MODEL-STEP](#)
[Catalogs - Full Line BURNDY Catalog](#)
[Sales Drawings - SD..029071-01](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-YCA252N-SPEC-EN | REV 8/2023