



YCA262NDTS, Copper compression terminal for terminating Copper conductor to switch pads, 2/0 Str, 1/2" Stud, 1-3/4" Spacing, Sealed oil tight and tin plated.

By Burndy
Catalog # [YCA262NDTS](#)



Cu Compression terminal Designed for terminating Cu Conductors to switch pads, 2/0 Str., 1/2 IN Stud, 2 Pad holes, Sealed oil tight and tin plated.

General

Catalog Number	YCA262NDTS
Connector Type	Terminal
Die Index	166
Material	Copper
Physical Attribute - Number of Holes	2
Plated	Y
Plating Type	Tin
Trade Name	HYLUG™
UPC	781810170168

Dimensions

Dimension - B Length inch	1.72 in
Dimension - Outside Diameter inch	0.71 in
Dimension - Pad Width inch	0.97 in
Dimension - Strip Length inch	1-13/16 in
Dimension - Stud Size inch	1/2 in
Physical Attribute - Tongue Angle	Straight

Conductor Related

Conductor - Copper Str Size	2/0 AWG
-----------------------------	---------

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	25
Minimum Pack Quantity	1
Pallet Quantity	5800

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - sd029071-01](#)
[Specifications - YCA262NDTS](#)