



Uninsulated Right Angle Ring Terminal For 12 - 10 AWG

By Burndy
Catalog # [YAV10R3](#)



Uninsulated Right Angle Ring Terminal For 12 - 10 AWG.

General

Connector Type	Ring Terminal
Construction Material - Main	Copper
EU RoHS Indicator	Contact Manufacturer
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Finish Type	Tin-Plated
Insulation	N
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	HYLUG
Trade Name	HYLUG™
Type	YAV-R
UPC	781810025215

Dimensions

Dimension - B Length fraction	2/5 in
Dimension - B Length inch	0.41 in
Dimension - Bolt Size fraction	1/4
Dimension - G inch	0.61 in
Dimension - Hole Size fraction	1/4
Dimension - Hole Size inch	0.27 in
Dimension - Hole Size mm	7 mm
Dimension - L Length Overall mm	14 mm
Dimension - Length Overall inch	0.56 in
Dimension - N inch	0.23 in
Dimension - Outside Diameter inch	0.22 in
Dimension - Pad Width inch	0.47 in
Dimension - Stud Size inch	1/4
Dimension - Z inch	0.28 in

Conductor Related

Conductor - Copper Str Aircraft Size	AN 12;AN 10
Conductor - Copper Str Aircraft Size Range	AN 12-AN 10
Conductor - Copper Str Size	12;10
Conductor - Copper Str Size Range	12 AWG - 10 AWG
Conductor Size	12 - 10 AWG
Conductor Type	<ul style="list-style-type: none">• CU C Solid-Size• CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	500
Minimum Pack Quantity	500
Pallet Quantity	99999

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Installation Manuals - Copper Code Standard Terminals Tooling and Installation Instructions](#)
[Sales Drawings - 50094165](#)
[Technical Solutions - BURNDY_YAV10R3_Specsheet](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-YAV10R3-SPEC-EN | REV 1/2024