



# YCA282N90, Copper Overhead Compression Terminal, 4/0 AWG, 2-Hole, 90 Degree Angle Tongue

By Burndy  
Catalog # [YCA282N90](#)



Cu Overhead Compression Terminal Designed for terminating Cu Conductors to Switch Pads, 4/0 AWG, 2 Pad Holes, 90 Deg, 168 Index.

## General

Connector Type	Terminal
Die Index	168;208
Material	Copper
Oxide Inhibitor Type	Penetrox A
Physical Attribute - Number of Crimps Required	1
Physical Attribute - Number of Holes	2
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Trade Name	HYLUG™
UPC	781810289259
UPC 12 Digit	7818102892599

## Dimensions

Dimension - B Length fraction	1-5/8 in
Dimension - B Length inch	1.62 in
Dimension - Hole Size fraction	5/9
Dimension - Hole Size inch	0.56 in
Dimension - Hole Size mm	14 mm
Dimension - N inch	0.63 in
Dimension - Outside Diameter inch	0.89 in
Dimension - Pad Width inch	1.22 in
Dimension - Strip Length inch	1 11/16
Dimension - Stud Size inch	33/64
Physical Attribute - Tongue Angle	90 Degree

## Conductor Related

Conductor - Copper Str Size	4/0 AWG
Conductor - Copper Str Size Range	4/0 AWG

## Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Carton Quantity	4
Minimum Pack Quantity	1
Pallet Quantity	2304

## Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Sales Drawings - 50100070](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
BRDY-YCA282N90-SPEC-EN | REV 5/2024