

Compression Terminal

By Burndy
Catalog # YAV150FM16

Non Insulated Cu Tubular Terminal, 1 Hole, W/Insp Window, 150 mm, 16 mm Stud, 3.00 IN L, Compression, 17 Index, 29 mm Strip Length.



Application

Metric Wire Termination

General

Connector Type	METRIC
Die Index	17
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Metric Terminals
UPC	781810322055
UPC 12 Digit	7818103220555

Dimensions

Dimension - B Length inch	1.06 in
Dimension - Bolt Size fraction	5/8
Dimension - Bolt Size inch	0.63
Dimension - Hole Size fraction	5/8
Dimension - Hole Size inch	0.69
Dimension - Hole Size mm	17.5 mm
Dimension - L Length Overall mm	76 mm
Dimension - Length Overall inch	3 in
Dimension - N inch	0.66 in
Dimension - Outside Diameter inch	0.88 in
Dimension - Pad Width inch	1.29 in
Dimension - Strip Length inch	1.14 in
Dimension - Stud Size fraction	5/8
Dimension - Z inch	0.67 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper Str Size	150 mm ²
Conductor - Material	COPPER
Conductor Size	150 mm ²
Conductor Type	CLASS 5

Certifications and Compliance

Standards - RoHS Compliance Status	CM
------------------------------------	----

Logistics

Minimum Pack Quantity	100
-----------------------	-----

Product Assets

[3D Models - YAV150FM16_MODEL-PDF](#)
[3D Models - YAV150FM16_MODEL-STEP](#)
[3D Models - YAV150FM16_MODEL-IGES](#)
[Catalogs - Full Line BURNDY Catalog](#)
[Sales Drawings - 50025612](#)

