

## YAV185FM14, Compression Terminal

By Burndy  
Catalog # YAV185FM14



Non Insulated Cu Tubular Terminal, 1 Hole, W/Insp Window, 185 mm, 14 mm Stud, 2.97 IN L, Compression, 18 Index, 29 mm Strip Length.

### Application

Metric Wire Termination

### General

Catalog Number	YAV185FM14
Connector Type	METRIC
Die Index	18
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Metric Terminals
UPC	781810322130
UPC 12 Digit	7818103221300

### Dimensions

Dimension - B Length inch	1.19 in
Dimension - Bolt Size fraction	1/2
Dimension - Bolt Size inch	0.5
Dimension - Hole Size fraction	1/2
Dimension - Hole Size inch	0.56
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	75.4 mm
Dimension - Length Overall inch	2.97 in
Dimension - N inch	0.55 in
Dimension - Outside Diameter inch	0.95 in
Dimension - Pad Width inch	1.40 in
Dimension - Strip Length inch	1.14 in
Dimension - Stud Size fraction	1/2
Dimension - Z (inch)	0.57 in
Physical Attribute - Tongue Angle	Straight

### Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

### Conductor Related

Conductor - Copper Str Size	185 mm2
Conductor - Material	COPPER
Conductor Size	185 mm2
Conductor Type	CLASS 5

### Certifications And Compliance

Standards - RoHS Compliance Status	CM
------------------------------------	----

### Logistics

Minimum Pack Quantity	100
-----------------------	-----

### Product Assets

- [3D Models - YAV185FM14\\_MODEL-PDF](#)
- [3D Models - YAV185FM14\\_MODEL-IGES](#)
- [3D Models - YAV185FM14\\_MODEL-STEP](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section C - Compression Connections](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_yavm\\_lineart](#)
- [Sales Drawings - 50025612](#)
- [Specifications - YAV185FM14](#)



A Hubbell brand