



YCA282NSV

By Burndy
Catalog # [YCA282NSV](#)

Cu Overhead compression terminal designed for terminating Cu Conductors to switch pads, 4/0 Str., 1/2 IN Stud, 2 Pad holes, Silver plating.



General

Connector Type	Terminal
Die Index	168;208
Material	Copper
Physical Attribute - Number of Crimps Required	1
Physical Attribute - Number of Holes	2
Plated	Y
Plating Type	Silver
Prefilled Oxide Inhibitor	N
Trade Name	HYLUG™
UPC	781810185735

Dimensions

Dimension - B Length fraction	1-31/50 in
Dimension - B Length inch	1.62 in
Dimension - D inch	3.00 in
Dimension - Hole Size fraction	5/9
Dimension - Hole Size inch	0.56 in
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	136 mm
Dimension - Length Overall inch	5.35 in
Dimension - N inch	0.63 in
Dimension - Outside Diameter inch	0.89 in
Dimension - Pad Width inch	1.22 in
Dimension - Strip Length inch	1 11/16
Dimension - Stud Size inch	1/2
Dimension - Z inch	0.62 in
Physical Attribute - Tongue Angle	Straight

Conductor Related

Conductor - Copper Str Size 4/0 AWG

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	40
Minimum Pack Quantity	1
Pallet Quantity	9600

Product Assets

[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - SD..029071-02](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-YCA282NSV-SPEC-EN | REV 8/2023