



YCA282NTN, Copper compression terminal, 2-hole, 1/2" Stud, 1-3/4" Spacing, Tin Plated

By Burndy
Catalog # YCA282NTN

Cu Compression terminal, 2 Holes, 4/0 (7,12,19) AWG STR, 1/2 IN Stud, 1.75 IN Spacing, 168 or 208 Index, Tin plated.



General

Catalog Number	YCA282NTN
Connector Type	Terminal
Die Index	168;208
Material	Copper
Physical Attribute - Number of Crimps Required	1
Physical Attribute - Number of Holes	2
Plated	Y
Plating Type	Tin - Electro Plated
Prefilled Oxide Inhibitor	N
Trade Name	HYLUG™
UPC	781810055793

Dimensions

Dimension - B Length fraction	1-69/100 in
Dimension - B Length inch	1.62 in
Dimension - D inch	3.00 in
Dimension - Hole Size fraction	5/9
Dimension - Hole Size inch	0.56 in
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	136 mm
Dimension - Length Overall inch	5.35 in
Dimension - N inch	0.63 in
Dimension - Outside Diameter inch	0.89 in
Dimension - Pad Width inch	1.22 in
Dimension - Strip Length inch	1 11/16
Dimension - Stud Size inch	1/2
Dimension - Z (inch)	0.62 in
Physical Attribute - Tongue Angle	Straight

Conductor Related

Conductor - Copper Str Size	4/0 AWG
Conductor - Copper Str Size Range	4/0 AWG

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	25
Minimum Pack Quantity	1
Pallet Quantity	3700

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - SD..029071-01](#)
[Specifications - YCA282NTN](#)