

Compression Terminal

By Burndy
Catalog # [YAV240FM16](#)

Non Insulated Cu Tubular Terminal, 1 Hole, W/Insp Window, 240 mm, 16 mm Stud, 3.37 IN L, Compression, 20 Index, 33 mm Strip Length.



Application

Metric Wire Termination

General

Connector Type	METRIC
Die Index	20
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Metric Terminals
UPC	781810322406
UPC 12 Digit	7818103224066

Dimensions

Dimension - B Length inch	1.27 in
Dimension - Bolt Size fraction	5/8
Dimension - Bolt Size inch	0.63
Dimension - Hole Size fraction	5/8
Dimension - Hole Size inch	0.69
Dimension - Hole Size mm	17.5 mm
Dimension - L Length Overall mm	85.5 mm
Dimension - Length Overall inch	3.37 in
Dimension - N inch	0.66 in
Dimension - Outside Diameter inch	1.06 in
Dimension - Pad Width inch	1.55 in
Dimension - Strip Length inch	1.30 in
Dimension - Stud Size fraction	5/8
Dimension - Z inch	0.67 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Material	COPPER
Conductor Size	240 mm ²
Conductor Type	CLASS 5

Certifications and Compliance

Standards - RoHS Compliance Status	CM
------------------------------------	----

Logistics

Carton Quantity	100
Minimum Pack Quantity	5
Pallet Quantity	4800

Product Assets

[3D Models - YAV240FM16_MODEL-PDF](#)
[3D Models - YAV240FM16_MODEL-STEP](#)
[3D Models - YAV240FM16_MODEL-IGES](#)
[Catalogs - Full Line BURNDY Catalog](#)
[Sales Drawings - 50025612](#)

