



YAV26L2TC38FX, Cu Compression, 2-Hole, 3/8" Stud, 1" Spacing, Standard Barrel, 2/0 Flex

By Burndy

Catalog # [YAV26L2TC38FX](#)



2/0 Flex G,H,I,K,M,DLO, 2/0 AWG CU, Two Hole, 3/8 Stud Size, 1 Hole Spacing, Standard Barrel, Inspection Window, Internal Chamfer, Tin Plated, UL/CSA, 90°C, Up to 35kV, Black Color Code, 13 Die Index.

Application

Wire Termination

General

Catalog Number	YAV26L2TC38FX
Color Code	Black
Connector Type	STANDARD BARREL
Die Index	13
EU RoHS Indicator	Yes
Feature - Barrel Style	<ul style="list-style-type: none">• Chamfered• Skived
Feature - Barrel Type	Standard
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	2
Physical Attribute - Tongue Type	Standard
Plated	Y
Plating Type	Tin
Sub Brand	HYLUG
Temperature Rating	194
Trade Name	HYLUG™
Type	Standard Barrel, Tin Plated
UPC	781810021767
UPC 12 Digit	7818100217677

Dimensions

Dimension - B Length fraction	13/16 in
Dimension - B Length inch	0.81 in
Dimension - Bolt Hole Size inch	0.41 in
Dimension - Bolt Size fraction	3/8
Dimension - Bolt Size inch	0.38
Dimension - Hole Size fraction	3/8
Dimension - Hole Size inch	0.41
Dimension - Hole Size mm	10.4 mm
Dimension - L Length Overall mm	79 mm
Dimension - Length Overall inch	3.12 in
Dimension - N inch	0.41 in
Dimension - Outside Diameter inch	0.63 in
Dimension - Pad Width inch	0.93 in
Dimension - Strip Length inch	13/16 in
Dimension - Stud Size fraction	3/8
Dimension - Z (inch)	0.43 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper DLO Size	2/0 AWG
Conductor - Copper DLO Size Range	2/0 AWG
Conductor - Copper Flex G Size	"2/0 AWG"
Conductor - Copper Flex G Size Range	2/0 AWG
Conductor - Copper Flex H Size	"2/0 AWG"
Conductor - Copper Flex H Size Range	2/0 AWG
Conductor - Copper Flex I Size	"2/0 AWG"
Conductor - Copper Flex I Size Range	2/0 AWG
Conductor - Copper Flex K Size	"2/0 AWG"
Conductor - Copper Flex K Size Range	2/0 AWG
Conductor - Copper Flex M Size	"2/0 AWG"
Conductor - Copper Flex M Size Range	2/0 AWG
Conductor - Copper Solid Size	2/0 AWG
Conductor - Copper Solid Size Range	2/0 AWG
Conductor - Copper Str Compact Size	"2/0 AWG"
Conductor - Copper Str Navy Size	125
Conductor - Copper Str Navy Size Range	125 (61) Navy
Conductor - Copper Str Size	"2/0 AWG"
Conductor - Copper Str Size Range	2/0 AWG
Conductor - CopperWeld Str Size	2/0 WELD
Conductor - CopperWeld Str Size Range	2/0 WELD
Conductor - Material	COPPER
Conductor Size	2/0 AWG
Conductor Type	CODE/FLEX
Wire Size	2/0 AWG

Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

Logistics

Carton Quantity	100
Minimum Pack Quantity	1
Pallet Quantity	18500

Product Assets

[3D Models - YAV26L2TC38FX_MODEL-IGES](#)
[3D Models - YAV26L2TC38FX_MODEL-PDF](#)
[3D Models - YAV26L2TC38FX_MODEL-STEP](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section C - Compression Connections](#)
[Customer Notices - Prop 65 Notice](#)
[Installation Manuals - Copper Flex Standard Terminals Tooling and Installation Instructions](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - SE..208119-01](#)
[Specifications - YAV26L2TC38FX](#)
[Video - HYDENT Compression Terminal Overview Video](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY-YAV26L2TC38FX-SPEC-EN | REV 8/2024