



YCAK32R2G1, Aluminum compression terminal, 2-Hole, 3/0 AWG Cu/Al, 350, 397.5, 336.4

By Burndy
Catalog # [YCAK32R2G1](#)



Cast Aluminum Compression Terminal, 2 Pad Holes, 3/0 AWG (7,19) Cu & Al, 350 (19,37) & 397.5 (19) kcmil, 336.4 (18 - 1, 26 - 7), 317 or 705 Index.

General

Die Index	317;705
Material	Aluminum, Cast
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Trade Name	HYLUG™
UPC	781810016619
UPC 12 Digit	7818100166199

Dimensions

Dimension - B Length inch	3 in
Dimension - Bolt Hole Size inch	0.56 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Dimension - L Length Overall mm	184 mm
Dimension - Length Overall inch	7.25 in

Conductor Related

Conductor - ACSR Str Size	336.4 kcmil
Conductor - AL Str Size	350 kcmil;397.5 kcmil
Conductor - AL Str Size Range	350 kcmil - 397.5 kcmil

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Product Cross Section Image\(s\) - BUR_YCAK27R2G2_LineArt](#)
[Sales Drawings - SD062358-01](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-YCAK32R2G1-SPEC-EN | REV 5/2024