




YDS2W, Copper Single Sleeve Full Tension Splice

By Burndy
Catalog # [YDS2W](#)



HYSPLICE Single Sleeve Full Tension Splice, Accommodates Wire: #2 Cu Sol (Hard, Medium, or Soft Drawn), Die Index: 163, Made of copper tubing, Installed with standard tools and dies.

Application

For Solid Copper Conductors

General

Catalog Number	YDS2W
Connector Type	Splice
Die Index	163
EU RoHS Indicator	Yes
Material	Copper
Oxide Inhibitor Type	Penetrox E
Physical Attribute - Number of Crimps Required	2
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Sub Brand	HYSPLICE
Trade Name	HYSPLICE™
Type	YDS-W
UPC	781810868270

Dimensions

Dimension - B Length fraction	1-3/4 in
Dimension - B Length inch	1.75 in
Dimension - L Length Overall mm	95 mm
Dimension - Length Overall inch	3.75 in
Dimension - Outside Diameter inch	0.48 in

Conductor Related

Conductor - Copper Solid Size	2 AWG
Conductor - Copper Str Size	3 AWG

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	100
Minimum Pack Quantity	1
Pallet Quantity	11100

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Catalogs - Section H - Overhead Distribution](#)
[Customer Notices - Prop 65 Notice](#)
[Product Cross Section Image\(s\) - BUR_YDS_LineArt](#)
[Sales Drawings - SD..015142-02](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-YDS2W-SPEC-EN | REV 6/2024