



YDS6WK, Copper Full Tension Splice

By Burndy
Catalog # [YDS6WK](#)



HYSPLICE Single Sleeve Full Tension Splice, Accommodates Wire: #6 Sol COPPERWELD, Die Index: 162 or 276, Made of copper tubing, Installed with standard tools and dies.

Application

For Copperweld Conductors

General

Connector Type	Splice
Construction Material - Main	Copper
Die Index	276;162
EU RoHS Indicator	Yes
Material	Copper
Physical Attribute - Number of Crimps Required	6
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	N
Sub Brand	HYSPLICE
Trade Name	HYSPLICE™
Type	YDS-K
UPC	781810014585

Dimensions

Dimension - B Length inch	1.77 in
Dimension - L Length Overall mm	103 mm
Dimension - Length Overall inch	4.04 in
Dimension - Outside Diameter inch	0.48 in

Conductor Related

Conductor - Copper Solid Size	6 AWG
Conductor - Copper Str Size	1 AWG
Conductor - CopperWeld C Solid Size	6 AWG
Conductor - CopperWeld Solid Size Range	6 AWG

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	150
Minimum Pack Quantity	1
Pallet Quantity	7200

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - SC021055-01](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-YDS6WK-SPEC-EN | REV 8/2023