

# Compression Terminal

By Burndy  
Catalog # [YAV3002M20](#)

Hylug Copper tubing Compression terminals,300 mm<sup>2</sup>,M20 Stud, 2 Holes,Tin Plated.



## Application

Metric Wire Termination

## General

Connector Type	METRIC
Die Index	22
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Metric Terminals
UPC	781810638163
UPC 12 Digit	7818106381633

## Dimensions

Bolt Size	M20
Dimension - B Length inch	6.9 in
Dimension - Bolt Size fraction	7/8
Dimension - Bolt Size inch	0.88
Dimension - Hole Size fraction	7/8
Dimension - Hole Size inch	0.94
Dimension - Hole Size mm	23.8 mm
Dimension - L Length Overall mm	146 mm
Dimension - Length Overall inch	5.73 in
Dimension - N inch	0.88 in
Dimension - Outside Diameter inch	1.19 in
Dimension - Pad Width inch	44.2 in
Dimension - Strip Length inch	1.38 in
Dimension - Stud Size fraction	7/8
Dimension - Z inch	0.89 in
Physical Attribute - Tongue Angle	Straight
Thickness - Pad	0.27 in

## Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

## Conductor Related

Conductor - Copper Str Size	300 mm <sup>2</sup> ,600 AWG
Conductor - Material	COPPER
Conductor Size	300 mm <sup>2</sup>
Conductor Type	CLASS 2

## Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

## Logistics

Minimum Pack Quantity	5
-----------------------	---

## Product Assets

[3D Models - YAV3002M20\\_MODEL-STEP](#)  
[3D Models - YAV3002M20\\_MODEL-PDF](#)  
[3D Models - YAV3002M20\\_MODEL-IGES](#)  
[Catalogs - Full Line BURNDY Catalog](#)  
[Sales Drawings - 50025887](#)

