




YDS8W, Copper, Single Sleeve Full Tension Splice

By Burndy
Catalog # [YDS8W](#)



HYSPLICE Single Sleeve Full Tension Splice, Accommodates Wire: #8 Cu Sol (Hard, Medium, or Soft Drawn), Die Index: 171, Made of copper tubing, Installed with standard tools and dies.

Application

For Solid Copper Conductors

General

Connector Type	Splice
Construction Material - Main	Copper
Die Index	171
EU RoHS Indicator	Yes
Material	Copper
Oxide Inhibitor Type	Penetrox E
Physical Attribute - Number of Crimps Required	1
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Sub Brand	HYSPLICE
Trade Name	HYSPLICE™
Type	YDS-W
UPC	781810820957

Dimensions

Dimension - B Length inch	0.70 in
Dimension - L Length Overall mm	42 mm
Dimension - Length Overall inch	1.65 in
Dimension - Outside Diameter inch	0.25 in

Conductor Related

Conductor - Copper Solid Size 8 AWG

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	100
Minimum Pack Quantity	1

Product Assets

[3D Models - YDS8W_MODEL-STEP](#)
[3D Models - YDS8W_MODEL-IGES](#)
[3D Models - YDS8W_MODEL-PDF](#)
[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - SD..015142-02](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-YDS8W-SPEC-EN | REV 8/2023