

YG14BTC26 Compression Bus Bar Connector

By Burndy
Catalog # YG14BTC26



Copper Compression Bus Bar Connector, 1/4 " Thick Steel and Copper Busbar to 2/0 AWG - # 2 AWG Str.

Features

- Compression Busbar Connector
- Easier to use than Exothermic Connections
- Ideally suited for cellular tower applications.

General

Connector Type	Tap
Material	Copper Alloy
Physical Attribute - Number of Crimps Required	1
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Trade Name	HYGROUND®
UPC	781810267806
UPC 12 Digit	7818102678066

Dimensions

Dimension - B Length fraction	64/79 in
Dimension - B Length inch	0.81 in
Dimension - Pad Width inch	1.50 in

Conductor Related

Conductor - Copper Flex G Tap	2 AWG;1 AWG;1/0 AWG;2/0 AWG
Conductor - Copper Flex G Tap Range	2 AWG-2/0 AWG
Conductor - Copper Solid Run	1/4" bus bar
Conductor - Copper Solid Tap	1 AWG;1/0 AWG
Conductor - Copper Solid Tap Range	1 AWG-1/0 AWG
Conductor - Copper Str Tap	2 AWG;1 AWG;1/0 ;2/0 AWG
Conductor - Copper Str Tap Range	2 AWG-2/0 AWG
Conductor Type	<ul style="list-style-type: none"> • CU C Str-Size • CU C Solid-Size • Bar-Size

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	Yes
Industry Standard(s)	<ul style="list-style-type: none"> • UL467 • UL 486A • CSA C22.2 No 65
Standards - Industry Standards Met	<ul style="list-style-type: none"> • UL467 • UL 486A • CSA C22.2 No 65
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	20
Minimum Pack Quantity	1
Pallet Quantity	5800

Product Assets

[3D Models - YG14BTC26_MODEL-STEP](#)
[3D Models - YG14BTC26_MODEL-IGES](#)
[3D Models - YG14BTC26_MODEL-PDF](#)
[Catalogs - Full Line BURNDY Catalog](#)
[Sales Drawings - SD..214246-01](#)

