

Compression Terminal

By Burndy
Catalog # [YAV630F2M12](#)

Cu Compression Metric Lug Terminal, 2 Holes W/InspWindow, 630 mm², M12 Stud.



Application

Metric Wire Termination

General

Connector Type	METRIC
Die Index	31
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Metric Terminals
UPC	781810643020
UPC 12 Digit	7818106430200

Dimensions

Dimension - B Length inch	2
Dimension - Bolt Size fraction	1/2
Dimension - Bolt Size inch	0.5
Dimension - Hole Size fraction	1/2
Dimension - Hole Size inch	0.53
Dimension - Hole Size mm	13.5 mm
Dimension - L Length Overall mm	155 mm
Dimension - Length Overall inch	6.10 in
Dimension - Pad Width inch	2.69
Dimension - Strip Length inch	2.17 in
Dimension - Stud Size fraction	1/2
Dimension - Z (inch)	0.55 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper Str Size	630 mm ²
Conductor - Material	COPPER
Conductor Size	630 mm ²
Conductor Type	CLASS 2

Certifications And Compliance

Certification - CSA Approved	No
Industry Standard(s)	UL 486A-486B
Standards - RoHS Compliance Status	CM

Logistics

Minimum Pack Quantity	2
-----------------------	---

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Product Cross Section Image\(s\) - BUR_yavm_lineart](#)
[Sales Drawings - 50025888](#)