

Compression Terminal

By Burndy
Catalog # [YAV630M20](#)

Copper Tubing Terminal, 1 Hole W/insp window, 630 mm Class 2, 29 Index, 20 mm Stud.



Application

Metric Wire Termination

General

Connector Type	METRIC
Die Index	29
Feature - Barrel Style	<ul style="list-style-type: none"> • Chamfered • Skived
Feature - Barrel Type	Standard
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Metric Terminals
UPC	781810323830
UPC 12 Digit	7818103238300

Dimensions

Dimension - B Length fraction	2 in
Dimension - B Length inch	2.00 in
Dimension - Bolt Size fraction	7/8
Dimension - Bolt Size inch	0.88
Dimension - Hole Size fraction	7/8
Dimension - Hole Size inch	0.94
Dimension - Hole Size mm	23.8 mm
Dimension - L Length Overall mm	125.2mm
Dimension - Length Overall inch	0.38 in
Dimension - N inch	0.88 in
Dimension - Outside Diameter inch	1.69 in
Dimension - Pad Width inch	0.46 in
Dimension - Strip Length inch	2.17 in
Dimension - Stud Size fraction	7/8
Dimension - Z inch	0.89 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Material	COPPER
Conductor Size	630 mm ²
Conductor Type	CLASS 2

Certifications and Compliance

Standards - RoHS Compliance Status CM

Logistics

Minimum Pack Quantity	2
-----------------------	---

Product Assets

[3D Models - YAV630M20_MODEL-IGES](#)
[3D Models - YAV630M20_MODEL-PDF](#)
[3D Models - YAV630M20_MODEL-STEP](#)
[Catalogs - Full Line BURNDY Catalog](#)
[Sales Drawings - 50025521](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-YAV630M20-SPEC-EN | REV 8/2023