



# YGF342N Grounding Plate, 250-500 kcmil Cu, 2-Hole, 1/2" Stud, 1-3/4" Spacing

By Burndy  
Catalog # [YGF342N](#)

Compression Grounding Plate; Copper; 2-Hole;  
Accommodates: 250 - 500 kcmil; 1/2" Stud; 1-3/4" Stud Hole Spacing.



## General

Die Index	1011
Material	Copper
Physical Attribute - Number of Crimps Required	2
Physical Attribute - Number of Tapped Holes	2
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Trade Name	HYGROUND®
UPC	781810002131
UPC 12 Digit	7818100021311

## Dimensions

Dimension - D inch	3.25 in
Dimension - Height fraction	4-31/50 in
Dimension - Height inch	4.62 in
Dimension - L Length Overall mm	137 mm
Dimension - Length Overall inch	5.40 in
Dimension - Pad Width inch	2.00 in
Dimension - Thread Size	3/8 -16
Physical Attribute - Tongue Angle	Straight

## Conductor Related

Conductor - Copper Str Size	250 kcmil;300 kcmil;350 kcmil;400 kcmil;450 kcmil;500 kcmil
Conductor - Copper Str Size Range	250 kcmil-500 kcmil
Conductor Type	CU C Str-Size

## Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	NEMA Size Holes
Standards - Industry Standards Met	UL467;IEEE 837
Standards - RoHS Compliance Status	EX
UL Listed	Yes

## Logistics

Minimum Pack Quantity	4
-----------------------	---

## Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Product Cross Section Image\(s\) - BUR\\_YGF\\_Lineart](#)  
[Sales Drawings - sd082518-01](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
BRDY-YGF342N-SPEC-EN | REV 5/2024