

YGHA26NTNNP Compression Grounding Lug, 2/0 AWG Cu, 2-Hole, 1/2" Stud, 1-3/4" Spacing, Tin Plated, No Oxide Inhibitor



By Burndy
Catalog # [YGHA26NTNNP](#)

Tin plated Heavy Duty Irreversible Compression Terminals without oxide inhibitor.

General

Catalog Number	YGHA26NTNNP
Connector Type	Terminal
Die Index	15
Material	Copper
Physical Attribute - Number of	1
Crimps Required	
Plated	Y
Plating Type	Electro Tin plated
Trade Name	HYLUG™
Type	Terminals
UPC	781810375488
UPC 12 Digit	7818103754888

Dimensions

Dimension - B Length fraction	39/47 in
Dimension - B Length inch	0.83 in
Dimension - D inch	1.27 in
Dimension - Hole Size inch	0.56 in
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	67 mm
Dimension - Length Overall inch	2.63 in
Dimension - N inch	0.63 in
Dimension - Outside Diameter inch	0.71 in
Dimension - Pad Width inch	0.97 in
Dimension - Z (inch)	0.64 in
Physical Attribute - Tongue Angle	Straight

Conductor Related

Conductor - Copper Str Size	2/0 AWG
Conductor - Copper Str Size Range	2/0 AWG
Conductor Type	<ul style="list-style-type: none"> • CU C Str-Size • CU C Solid-Size

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Standards - Industry Standards Met	UL467;UL468A-468B;IEEE 837
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Carton Quantity	25
Minimum Pack Quantity	1
Pallet Quantity	9600

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - SD..211241-01](#)
[Specifications - YGHA26NTNNP](#)