

Uninsulated Ring Terminal For 6 AWG

By Burndy
Catalog # YAV6CLBOX500



Uninsulated Ring Terminal For 6 AWG.

General

Connector Type	Ring Terminal
Die Index	39
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Material Composition	<ul style="list-style-type: none"> • DLP Copper • Tin Plating
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Ring Tongue
UPC	781810329986

Dimensions

Dimension - B Length fraction	1/2 in
Dimension - B Length inch	0.47 in
Dimension - Bolt Hole Size inch	0.27 in
Dimension - Bolt Size fraction	1/4
Dimension - Hole Size mm	7 mm
Dimension - Length Overall inch	1.28 in
Dimension - N inch	0.25 in
Dimension - Outside Diameter inch	0.31 in
Dimension - Pad Width inch	0.50 in
Dimension - Strip Length inch	1/2
Dimension - Stud Size inch	1/4 in
Dimension - Z inch	0.29 in
Physical Attribute - Tongue Angle	Straight

Conductor Related

Conductor - Copper Str Size	6 AWG
Conductor - Copper Str Size Range	6 AWG
Conductor Size	6 AWG
Conductor Type	<ul style="list-style-type: none"> • CU C Solid-Size • CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	500
Minimum Pack Quantity	500
Pallet Quantity	99999

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Sales Drawings - 50094161](#)
[Technical Solutions - BURNDY_YAV6CLBOX500_Specsheet](#)

