

Uninsulated Right Angle Ring Terminal For 6 AWG

By Burndy
Catalog # [YAV6CRS](#)



Uninsulated Right Angle Ring Terminal For 6 AWG.

Application

For Use On Copper Commercial (Code) Cable, Type AN Aircraft Cable And Extra Flexible Conductors

General

Connector Type	Ring Terminal
Die Index	39
EU RoHS Indicator	Yes
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	HYLUG
Trade Name	HYLUG™
Type	Ring Tongue
UPC	781810025840

Dimensions

Dimension - B Length fraction	1/2 in
Dimension - B Length inch	0.50 in
Dimension - Bolt Hole Size inch	0.27 in
Dimension - Bolt Size fraction	1/4
Dimension - G inch	0.82 in
Dimension - Hole Size mm	7 mm
Dimension - L Length Overall mm	25 mm
Dimension - Length Overall inch	0.98 in
Dimension - N inch	0.25 in
Dimension - Outside Diameter inch	0.32 in
Dimension - Pad Width inch	0.50 in
Dimension - Strip Length inch	1/2
Dimension - Stud Size inch	1/4
Dimension - Z inch	0.28 in
Physical Attribute - Tongue Angle	90 Degree

Conductor Related

Conductor - Copper Str Aircraft Size	AN 6
Conductor - Copper Str Size	6
Conductor - Copper Str Size Range	6
Conductor Size	6 AWG
Conductor Type	<ul style="list-style-type: none"> • CU C Solid-Size • CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	200
Minimum Pack Quantity	1
Pallet Quantity	92800

Product Assets

- [3D Models - YAV6CRS_MODEL-PDF](#)
- [3D Models - YAV6CRS_MODEL-IGES](#)
- [3D Models - YAV6CRS_MODEL-STEP](#)
- [Catalogs - Full Line BURNDY Catalog](#)
- [Sales Drawings - 50094166](#)
- [Technical Solutions - BURNDY_YAV6CRS_Specsheet](#)

