




YGHC2C2 Compression Grounding C-TAP Connector

By Burndy
Catalog # YGHC2C2



Copper Compression C Connector, 6 AWG(Sol) - 2 AWG(Str), 1/4" Rod(Run) & 6 AWG(Sol) - 2 AWG(Str) (Tap).

Application

For Direct Burial Cables

General

Connector Type	Tap
Die Index	C
EU RoHS Indicator	Yes
Material	Copper
Physical Attribute - Number of Crimps Required	1
Plated	N
Plating Type	Unplated
Sub Brand	HYGROUND, HYTAP
Trade Name	HYTAP™
Type	Taps
UPC	781810221013
UPC 12 Digit	7818102210133

Dimensions

Dimension - B Length inch	0.75 in
Dimension - Height fraction	1-4/25 in
Dimension - Height inch	1.16 in
Dimension - L Length Overall mm	19 mm
Dimension - Length Overall inch	0.75 in

Conductor Related

Conductor - Copper Solid Run	6 AWG;5 AWG;4 AWG;3 AWG;2 AWG
Conductor - Copper Solid Run Range	6 AWG-2 AWG
Conductor - Copper Solid Tap	6 AWG;5 AWG;4 AWG;3 AWG;2 AWG
Conductor - Copper Solid Tap Range	6 AWG-2 AWG
Conductor - Copper Str Run	7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG
Conductor - Copper Str Run Range	7 AWG-2 AWG
Conductor - Copper Str Tap	7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG
Conductor - Copper Str Tap Range	7 AWG-2 AWG
Conductor - Rod Run	1/4 in
Conductor - Rod Run Range	1/4 in

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	<ul style="list-style-type: none"> • UL467 • IEEE 837 • IEEE 837 2014 Qualified • UL 468A-468B
Standards - Industry Standards Met	UL467;IEEE 837;IEEE 837 2014 Qualified;UL468A-468B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	50
Minimum Pack Quantity	1
Pallet Quantity	14800

Product Assets

- [3D Models - YGHC2C2_MODEL-IGES](#)
- [3D Models - YGHC2C2_MODEL-STEP](#)
- [3D Models - YGHC2C2_MODEL-PDF](#)
- [Catalogs - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Sales Drawings - SD086223-01](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-YGHC2C2-SPEC-EN | REV 8/2023