

Uninsulated Right Angle Ring Terminal For 8 AWG

By Burndy
Catalog # [YAV8CRS1](#)



Uninsulated Right Angle Ring Terminal For 8 AWG.

Application

For Use On Copper Commercial (Code) Cable, Type AN Aircraft Cable And Extra Flexible Conductors

General

Connector Type	Ring Terminal
Die Index	38
EU RoHS Indicator	Yes
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin
Sub Brand	HYLUG
Trade Name	HYLUG™
Type	Ring Tongue
UPC	781810025093

Dimensions

Dimension - B Length fraction	4/9 in
Dimension - B Length inch	0.44 in
Dimension - Bolt Size fraction	1/4
Dimension - G inch	0.78 in
Dimension - Hole Size fraction	1/4
Dimension - Hole Size inch	0.27 in
Dimension - Hole Size mm	7 mm
Dimension - L Length Overall mm	24 mm
Dimension - Length Overall inch	0.95 in
Dimension - N inch	0.2 in
Dimension - Outside Diameter inch	0.28 in
Dimension - Pad Width inch	0.41 in
Dimension - Strip Length inch	7/16
Dimension - Stud Size inch	1/4
Dimension - Z inch	0.28 in

Conductor Related

Conductor - Copper Str Aircraft Size	AN 8
Conductor - Copper Str Size	8
Conductor - Copper Str Size Range	8 AWG
Conductor Size	8 AWG
Conductor Type	<ul style="list-style-type: none"> • CU C Solid-Size • CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	1000
Minimum Pack Quantity	1
Pallet Quantity	99999

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Sales Drawings - 50094166](#)
[Technical Solutions - BURNDY_YAV8CRS1_Specsheet](#)

